

## Handheld Refractometer

Handheld Refractometer can be used for detection and analysis in sugar, pharmaceutical, beverage, petroleum, food, chemical industry production, scientific research, and teaching departments. Use visual aiming, optical dial reading, simple.

### 1. Handheld Refractometer Introduction

Innovation:

- 1: Portable design, easy to use;
- 2: LED cold light source replaces traditional sodium lamp and halogen tungsten lamp;
- 3: Color screen display, humanized operation interface;
- 4: The whole machine has passed TART and CE certification.

### 2. Handheld Refractometer Parameter

Model	JH-PR(Handheld Refractometer)
Refractive index nD	1.3330--1.5177 nD
Brix	0.0-59.9%
Resolution	0.0001nD 0.1%
Brix accuracy	±0.1%
Refractive index accuracy	±0.0002%
Display method	Digital Display
Temperature display range (minimum display value 0.1 °C)	0-40°C (Automatic temperature compensation)
Size	58*25*121mm
Weight	100g

### 3. Handheld Refractometer Feature And Application

1. Portable design, easy to use;
2. LED cold light source instead of the traditional sodium light lamp and halogen tungsten lamp;
3. Color screen display, user-friendly operation interface;
4. Handheld Refractometer has passed TART and CE certification.

### 4. Fields of use Handheld Refractometer

Sugar, pharmaceutical, beverage, petroleum, food, chemical industry production, scientific research, teaching departments of testing analysis.

### 5. Handheld Refractometer Details

The digital display brix meter measures the Brix of liquids, and can be used for detection and analysis in sugar, pharmaceutical, beverage, petroleum, food, chemical industry production, scientific research, and teaching departments. Use visual aiming, optical dial reading, simple.

### 6. Product Qualification

Jiahang Handheld Refractometer has obtained CE certification, TART certification, ISO quality management system certification, more than 10 software copyrights and multiple patents to ensure that each instrument has stable performance and excellent quality.

#### 7. **Deliver,Shipping And Serving**

We have a top R&D team returned from Europe and America, cooperate with our superb manufacturing team, professional sales team and dedicated service team, working together to provide customers with high-tech, high-quality products and efficient, convenient, Comprehensive pre-sales and after-sales professional services.

#### 8. **FAQ**

##### **How many years have your company made Handheld Refractometer ?**

22 years of scientific instrument manufacturer, laboratory solution provider!

##### **Which certificate do you have for your products?**

Jiahang has obtained CE certification, TART certification, ISO quality management system certification, more than 10 software copyrights and multiple patents to ensure that each instrument has stable performance and excellent quality.

##### **Will you will attend the fair to show your products?**

Yes, Every year we will participate in some internationally renowned exhibitions to launch our new products, such as Arablab, PICCTON, Analytica Russia, Lab Africa, Analytica Germany, Analytica Latin America and so on,we are looking forward to your visit.

##### **How about your company's R&D strength**

Possess strong R&D technical capabilities (a R&D team of more than 20 people, with an average degree of doctorate degree, graduated from well-known universities at home and abroad, with an average work experience of 8 years), able to deal with and solve product-related technical problems

##### **If OEM is acceptable ?**

Provide OEM customization service, product built-in software has autonomy, can customize development settings

##### **Are you a trading company or a manufacturer?**



☎ 0086 17721148861  
✉ bentian@jiahanglab.com  
🌐 www.jiahanglab.com  
📠 0086 021 59904405

100% manufacturer, no middlemen and distributors make the price difference, the price of the source factory is very advantageous; Jiahang is headquartered in Shanghai, China, has 15 service outlets and 2 production plants in China, and has sales in more than 10 countries overseas proxy.

### **How about your delivery time?**

"Generally, it will take 7 to 15 working days after receiving your advance payment. Depend on the quantity."

### **Which payment can be acceptable ?**

We could accept the payment by L/C, TF, Paypal , Western Union,etc.

### **Service**

We could provide Online instruction ; Real-time support by video-ca or voice-chat.

Any customer who cooperates for the first time promises to provide a production cost price trial opportunity to solve your worries about product quality problems.

Provide official product quality assurance documents that comply with legal benefits to escort you with worry-free after-sales service.