


W100



Product Description

W100 is an wifi industrial endoscope camera with HD camera. It adopts ergonomic design and uses mobile phone wifi connection app to display pictures it supports photo and video functions. This product is equipped with a small diameter HD camera withLED auxiliary lighting. The camera adopts a high-sensitivity chip, which can beused normally even in a dark working environment.

Safety and Maintenan

· Do not hit the camera violently and do not pull the cable.

· When used in an environment with sharp bumps, please use it carefully to prevent the waterproof protective layer of the probe from being scratched.

The camera probe is not made of heat-resistant and high-temperature materials. When checking the automobile engine, please ensure that the temperature in the engine drops to the normal temperature.

· When not in use, please ensure that the lens and the main unit are clean and dry, and avoid contact with oil, etc. or other corrosive and dangerous

·This product is not suitable for people with limited physical, sensory or mental abilities. · Do not allow children to touch and operate this equipment.

If the equipment is damaged, do not disassemble it by yourself. Please contact suppliers or agent for maintenance services.


·The product is an industrial endoscopy camera and is not intended for medical use or

Battery instructio

· Please use a 5V household charger that meets the safety regulations to charge the equipment. Fast charging is not supported.

· This device supports charging while using.

· If the device is not used for a long time, please ensure that it is charged at least once every 3 months to prevent irreparable damage caused by excessive discharge of the



1.Camera LED light (WIFI signal indicator): (1) LED blinks: ready to pair (2) LED stays on: connection is successful 2.Camera


3.The lens port lock switch

Function introduction


4.ON/OFF: Press and hold for 3 seconds to off/on 5.Typc-C charging port


6. Indicator A: (1) Red LED light keeps blinking: low battery (2) Red LED light stays on: charging status (3) Red LED light off while charging: battery fully charged


7. Indicator B: Working (green LED stays on)











1.APP does not display images

Unplug the camera connector, reassemble or restart the device

2.Lags happened during the photo outputting of the product Step 1: Keep the distance between the WiFi Industrial Endoscope and the phone/tablet

Step 2: Please check whether the product is fully charged, or restart the device, or reassemble the camera connector.

3. Imaging screen is not clear

The best imaging focal length of the product is: 2cm-10cm, please calibrate the distance to the object, or clean the front of the camera with a clean alcohol cloth.

4. Product charging

Please use 5V-1A charger to charge the aevice. ie pfast charging.

5. How to output picture on the phone

Step 1: Enter the cell phone connection menu on the Home page, press OKbutton to turn on WiFi

Step 2: Download APP


Step 3: Enter the WiFi interface in the phone settings, find the device WiFi, ANESOK-XXXX, click it and connect.

6. The camera is heat

It is normal for the camera to heat up, especially when the camera LED light is on at the highest brightness. But it does not affect normal use or service life.

Accessories installation Guid

Accessories: Protective ring*1, magnet *1, hook*1



arricra			
		Dual lens	Single lens
Camera diameter		7.9mm	7.9mm
Camera resolution		2 Megapixels	
Viewing angle		78°	70°
Auxiliary lighting		6+1 Einstellbare Helligkeits-LEDs	6 Einstellbare Helligkeits-LEDs
Fokussier -bereich	A Camera	20-100mm	20-100mm
	B Camera	20-50mm	

List: endoscope, manual, storage tube, magnet ,hook,

TYPE-C charge cable, instructions, Protective ring, Lens cable

Support camera probe resolution: 2 million pixels	Photo resolution: 1920*1080	
Video resolution: 1280*720	Port: TYPE-C charge cable	
Operating temperature: 32°F- 113°F(0°C-45°C)	Battery: 1000mAh	
Battery life: 4 hours	Battery charging time: 1.5 hours	

☼ ※ C **← F © RoHS ⊕ №** 210-123818

说明:正反折页尺寸:84*96mm