JIOPTICS

www.jioptics.com



Ring Laser Gyroscope High Precision Two Frequency Machine Shaking

Ring Laser Gyroscope High Precision Two Frequency Machine Shaking is a high-precision digital dual-frequency machine-shaking laser gyro developed and produced by Jloptics company. It has the advantages of high precision, simple power supply, high integration and digital output. It can measure the angular motion of the carrier around the sensitive axis and output two orthogonal square waves. It is widely used in the integration of positioning/navigation, fire control and flight control, surveillance and reconnaissance systems in the fields of missiles and their launch vehicles, ships, aircraft, drones, and armored vehicles.

Ring Laser Gyroscope High Precision Two Frequency Machine Shaking Overview

Ring Laser Gyroscope-JIO50 is a high-precision digital dual-frequency machine-shaking laser gyro developed and produced by Jloptics company. It has the advantages of high precision, simple power supply, high integration and digital output. It can measure the angular motion of the carrier around the sensitive axis and output two orthogonal square waves. It is widely used in the integration of positioning/navigation, fire control and flight control, surveillance and reconnaissance systems in the fields of missiles and their launch vehicles, ships, aircraft, drones, and armored vehicles.

JIO50-RLG is available in A, B and C models to meet your different needs.

Ring Laser Gyroscope High Precision Two Frequency Machine Shaking Features

Measure the rotation angle around its sensitive axis, and output two orthogonal square waves.

Performance

JIO50 -type laser gyroscope are shown in Table 1.

Table 1 Main Technical Indicators of Gyro

JIOPTICS

www.jioptics.com

serial number	parameter	unit	Grade A Grade B		Grade C	Remark
1	Zero bias	°/h	≤0.5			/
2	bias stability	°/h	≤0.5 % ≤1 %		≤3 %	100s , 1σ
3	Zero bias repeatability	°/h	≤0.5 %	≤1 %	≤3 %	1σ
4	random walk coefficient	°/h 1/2	≤2‰ ≤5‰ ≤9		≤9‰	/
5	Scale factor	"/pulse	3.370			/
6	Scale Factor Nonlinearity	ppm	≤5			/
7	Scale Factor Repeatability	ppm	≤5			1σ
8	Magnetic sensitivity	°/(h·Gs)	/			/
9	Maximum input angular rate	°/s	≥ ± 400			/
10	Start Time	the s	≤10			/

Environmental adaptability

- a) Working temperature : -40 $^\circ C$ ~ + 65 $^\circ C$
- b) Storage temperature: -45 $^\circ\!\!C$ ~ + 85 $^\circ\!\!C$
- c) Vibration: 9.6g in total;
- d) Shock: 30g/11ms (half sine) or 75g/6ms (half sine);
- e) Low pressure: 5000m above sea level.

Frequency (Hz)	10	100	200	300	400	500	800	2000
Power spectral density (g 2 /hz)	0.1	0.6	0.2	0.06	0.04	0.02	0.005	-6db

Power supply and electrical interface

a) Power supply Type: ± 5V , +15V Requirements: +5V - current 180mA , stability ± 50mV , ripple < 50mV -5V - current 60mA , stability ± 50mV , ripple < 50mV +15V - current 240mA , stability ± 100mV , ripple < 100mV b) Power consumption: < 6W

- c) Electrical interface type: J30J-25ZKP
- d) Interface definition: The definition of electrical interface pins is shown in Table 2.

Table 2 Electrical interface definition table

pin number	definition	Remark
1	+15V	power input

JIOPTICS

www.jioptics.com

2	+15VGND	+15V power ground		
3	NC	null		
4	GND	+5V , -5V power ground		
5	NC	null		
6	+5V	power input		
7	-5V	power input		
8	AOUT	Square wave output signal 1 (TTL level)		
9	BOUT	Square wave output signal 2 (TTL level)		
10	TMP3	Platinum resistance thermometer 3		
11	TCOMA	3 platinum resistance common terminals		
12	TMP1	Platinum resistance 1		
13	TMP2	Platinum resistance 2		
14	+15V	power input		
15	+15VGND	+15V power ground		
16	NC	null		
17	GND	+5V , -5V power ground		
18	NC	null		
19	+5V	power input		
20	-5V	power input		
twenty one	AOUT	Square wave output signal 1 (TTL level)		
twenty two	BOUT	Square wave output signal 2 (TTL level)		
twenty three	GND	+5V , -5V power ground		
twenty four	NC	Spinning Top		
25	NC	Spinning Top		
The models of platinum resistors 1 , 2, and 3 are Pt1000				

Reliability

MTBF: 10000h

Continuous working time: the continuous working time is not less than 24 hours after power-on.

Shape and mechanical interface

a) Weight: ≤620g ±20g

b) Shape and mechanical interface: as shown in Figure 1.

Continuous working time: the continuous working time is not less than 24 hours after power-on.

Tel:+86-13570832601

Email:sales@jioptics.com





Gyro appearance and installation diagram